

# Vector Fast Frame Rechargeable Lightbox w/Battery

VFF-LB-BAT-1-ASM

Vector Fast Frame™ Rechargeable Light Box is an innovative, collapsible SEG light box that sets up in seconds. Designed for ultimate flexibility, this sleek and portable display system delivers brilliant illumination without the need for external power sources, making it ideal for trade shows, retail environments, and pop-up events. The lithium-ion battery provides up to 15 hours of runtime on a single charge. This sleek 3.35" wide frame holds seamless, easy-to-change silicone edge graphics (SEG), which are easily applied to the front and back. Graphics can be easily swapped out to deliver new messages so you can use the frame again and again! Vector Fast Frame Rechargeable Light Box is lightweight, portable, and requires no tools, so assembly is a breeze. It packs down small, making travel and storage simple.



We are continually improving and modifying our product range and reserve the right to vary the specifications without prior notice. All dimensions and weights quoted are approximate and we accept no responsibility for variance. E&OE. See Graphic Templates for graphic bleed specifications

## features and benefits:

### Features and benefits:

- Collapsible, rechargeable slim light box 3'W x 7'H x 3.35"D
- Battery-operated and rechargeable with up to 15 hours runtime
- Digital display shows real-time battery life
- Collapsible, slim light box - freestanding, white frame
- Assembles in seconds
- Seamless and easy to change SEG push-fit graphics
- Front and back graphics available
- Highly portable and breaks down easy
- Includes carry bag
- Five year LED light warranty
- One year limited warranty against manufacturer defects

## dimensions:


| Hardware                                                                                                                                                                                                                                                                                                                                                        | Shipping                                                                                                                                                                                                                                                                                                                                           |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Assembled unit:<br><br>36"w x 75.5"h x 15.75"d<br>914mm w x 1918mm h x 400mm d<br><br>Approximate Weight: 24 lbs / 10.9 kg                                                                                                                                                                                                                                      | Packing case(s): 1 Box<br><br>Shipping dimensions:<br>44"L x 14.25"H x 11"D<br><br>Approximate shipping weight:<br>32bs / 14.5kg                                                                                                                                                                                                                   |
| Graphics                                                                                                                                                                                                                                                                                                                                                        | additional information:                                                                                                                                                                                                                                                                                                                            |
| Graphic material:<br>Back-lit Textile (dye-sublimated fabric)<br><br><br><br><br><br><br><br><br><br>Refer to related graphic templates for more information Visit:<br><br><a href="https://www.theexhibitorshandbook.com/downloads/download-graphic-templates">https://www.theexhibitorshandbook.com/downloads/download-graphic-templates</a><br>or click here | <b>Battery:</b><br>Lithium-ion 2700mAH<br><br><b>GROUND SHIPMENT ONLY FOR UNITS WITH BATTERY INSTALLED.</b><br><br><b>Charging:</b><br>The battery can be charged in or out of the unit. The display can be powered on during charging, however for maximum charging efficiency it is recommended that the display be powered off during charging. |

1




Lay frame on floor with and rotate the feet 90 degrees.

2



Unfold the frame by lifting the top.

3




Press the horizontal support pole into place as shown.

4




Tilt the unit on it's side opposite the digital display. Remove the two thumb screws to remove the battery tray.

5




Pull the battery tray forward to expose the battery and connectors.

6



Connect the battery and place the cable in the front of the tray. Close tray and install thumb screws.

7




Charge the unit with the included power supply by connecting to the charging port on the side of the frame.

8



Turn the unit on/off with the power button on the side of the frame.

9




The display shows battery capacity and voltage. Press the button to cycle through the options.

10



Green light on the power supply indicates battery is fully charged

11




Install graphics

## How to Apply & Remove Graphics



Installation and removal of SEG graphics is easy!

**Installation:** Push the SEG bead into each corner of the frame (1-4) with your thumb, then push the SEG bead into the middle of the run (5-8) and work your way around the perimeter of the frame until all beading is pushed in properly; if necessary, go around the perimeter again to ensure beading is secure in the extrusion profile.



**Note:** Keep the set up area clean by using a drop cloth, washing hands before set-up or by wearing gloves.

**Removal:** Use the pull tab located on the graphic and gently pull the graphic from the frame, going around the perimeter.



## Graphics Storage & Care

Graphics should be folded with the graphic facing inward and stored in a zip lock /sealable plastic bag. Spot clean by wiping with a damp white cloth. If washing is necessary, use a commercial size front-loading washing machine, gentle cycle with cool water. Line dry flat. Dry cleaning is NOT recommended to prevent shrinkage.